



CFL

CFL lamps provide the same amount of light (lumens) as regular incandescent lamps, but have a lower wattage rating. As a result, they consume less energy and cause less pollution. ALL STANDARD CFL lamps meet NEMA voluntary commitment on mercury content in CFL lamps and are all cULus listed, where applicable.

Specialty



20 W; MOL: 5 1/8 in. (130 mm)
Ø 2 9/32 in. (68 mm)

**High Power
Factor**



MOL: 5 1/16 in. (154 mm)
Ø 2 1/4 in. (57 mm)

Trilight

Order code	Description	Watts (W)	Base	Color temp. (K)	Lumen output (lm)	Average life (hrs)	CRI	Incandescent equivalent (W)	Case qty (inner/master)
High Power Factor									
58404	CF20/HPF/27K/SPIRAL/E26/STD	20	E26	2 700	1 200	10 000	82	75	12/48
Trilight									
58959	CF13/20/25/27K/SPIRAL/E26/STD	13 20 25	E26	2 700	900 1 200 1 550	8 000	80	60 75 100	6/48

T2 Spiral



MOL: 4 11/32 in. (110 mm)
Ø 2 5/32 in. (65 mm)

18 W



MOL: 5 1/16 in. (129 mm)
Ø 2 1/8 in. (54 mm)

26 W

Order code	Description	Watts (W)	Base	Color temp. (K)	Lumen output (lm)	Average life (hrs)	CRI	Incandescent equivalent (W)	Case qty (inner/master)
18 watts									
62832 ¹	CF18/T2/27K/SPIRAL/E26/STD	18	E26	2 700	1 250	12 000	82	75	6/48
62833 ¹	CF18/T2/30K/SPIRAL/E26/STD	18	E26	3 000	1 250	12 000	82	75	6/48
62834 ¹	CF18/T2/35K/SPIRAL/E26/STD	18	E26	3 500	1 250	12 000	82	75	6/48
26 watts									
63388 ¹	CF26/T2/27K/SPIRAL/E26/STD	26	E26	2 700	1 750	10 000	82	100	6/48
63389 ¹	CF26/T2/30K/SPIRAL/E26/STD	26	E26	3 000	1 750	10 000	82	100	6/48
63391 ¹	CF26/T2/41K/SPIRAL/E26/STD	26	E26	4 100	1 750	10 000	82	100	6/48
63392 ¹	CF26/T2/50K/SPIRAL/E26/STD	26	E26	5 000	1 750	10 000	82	100	6/48

GU24 Based



13 W: MOL: 3 5/8 in. (92 mm)
Ø 1 13/16 in. (46 mm)
18 W: MOL: 4 13/32 in. (112 mm)
Ø 1 1/8 in. (54 mm)
23 W: MOL: 4 13/32 in. (112 mm)
Ø 1 1/8 in. (54 mm)

Spiral (GU24)



23 W: MOL: 4 27/32 in. (123 mm)
Ø 2 1/8 in. (54 mm)

Dimmable Spiral (GU24)

Order code	Description	Watts (W)	Base	Color temp. (K)	Lumen output (lm)	Average life (hrs)	CRI	Incandescent equivalent (W)	Case qty (inner/master)
Spiral									
61843	CF13/T2/35K/SPIRAL/GU24/STD	13	GU24	3 500	880	10 000	82	60	6/48
61845	CF18/T2/27K/SPIRAL/GU24/STD	18	GU24	2 700	1 150	10 000	82	75	6/48
61846	CF23/T2/27K/SPIRAL/GU24/STD	23	GU24	2 700	1 600	10 000	82	100	6/48
61847	CF23/T2/41K/SPIRAL/GU24/STD	23	GU24	4 100	1 600	10 000	82	100	6/48
Spiral - Dimmable									
60921 ²	CF23/D/27K/SPIRAL/GU24/STD	23	GU24	2 700	1 500	10 000	82	100	6/48



High Wattage Spiral



Order code	Description	Watts (W)	Base	Color temp. (K)	Lumen output (lm)	Average life (hrs)	CRI	Incandescent equivalent (W)	Case qty (inner/master)
32 watts									
60932	CF32/27K/SPIRAL/E26/STD	32	E26	2 700	2 000	10 000	82	120	6/48
60933	CF32/30K/SPIRAL/E26/STD	32	E26	3 000	2 000	10 000	82	120	6/48
60936	CF32/50K/SPIRAL/E26/STD	32	E26	5 000	2 000	10 000	82	120	6/48
58412	CF32/65K/SPIRAL/E26/STD	32	E26	6 500	2 100	10 000	82	120	6/48
40 watts									
60940	CF40/35K/SPIRAL/E26/STD	40	E26	3 500	2 600	10 000	82	150	6/48
60942	CF40/50K/SPIRAL/E26/STD	40	E26	5 000	2 600	10 000	82	150	6/48
60943	CF40/65K/SPIRAL/E26/STD	40	E26	6 500	2 600	10 000	82	150	6/48
55 watts									
60922	CFL55/27K/SPIRAL/E26/STD	55	E26	2 700	3 700	10 000	82	300	6/48
60923	CFL55/50K/SPIRAL/E26/STD	55	E26	5 000	3 700	10 000	82	300	6/48
65 watts									
60924	CFL65/27K/SPIRAL/E26/STD	65	E26	2 700	4 300	10 000	82	300	6/48
60925	CFL65/50K/SPIRAL/E26/STD	65	E26	5 000	4 300	10 000	82	300	6/48
85 watts									
60926	CFL85/27K/SPIRAL/E26/STD	85	E26	2 700	5 400	10 000	82	350	6/12
60927	CFL85/50K/SPIRAL/E26/STD	85	E26	5 000	5 400	10 000	82	350	6/12
105 watts									
60929	CFL105/50K/SPIRAL/E39/STD	105	E39	5 000	6 500	10 000	82	400	6/12

