

CFL Lamps



PAR20

Order code	Description	Watts (W)	Base	Colour temp. (K)	CRI	Life L70 (hrs)	Lumen output (lm)	Traditional equivalent (W) Halogen	Case qty (master)
------------	-------------	--------------	------	---------------------	-----	-------------------	----------------------	--	----------------------

PAR20

59674	CF9/41K/PAR20/E26/ELUME	9	E26	4 100	82	8000	300	50	6/48
-------	-------------------------	---	-----	-------	----	------	-----	----	------



4 pack



12 pack

Order code	Description	Watts (W)	Base	Colour temp. (K)	CRI	Life L70 (hrs)	Lumen output (lm)	Traditional equivalent (W) Incandescent	Case qty (master)
------------	-------------	--------------	------	---------------------	-----	-------------------	----------------------	---	----------------------

T2 Spirals

62764	CF7/T2/27K/SPIRAL/E26/ELUME	7	E26	2 700	82	10 000	430	40	6/48
61020	CF9/T2/27K/SPIRAL/E26/ELUME	9	E26	2 700	82	10 000	550	40	6/48
62311	CF9/T2/41K/SPIRAL/E26/ELUME	9	E26	4 100	82	10 000	550	40	6/48
62765	CF11/T2/27K/SPIRAL/E26/ELUME	11	E26	2 700	82	10 000	730	40	6/48
61021	CF13/T2/27K/SPIRAL/E26/ELUME	13	E26	2 700	82	10 000	900	60	6/48
61024	CF13/T2/30K/SPIRAL/E26/ELUME	13	E26	3 000	82	10 000	900	60	6/48
61026	CF13/T2/35K/SPIRAL/E26/ELUME	13	E26	3 500	82	10 000	850	60	6/48
61029	CF15/T2/27K/SPIRAL/E26/ELUME	15	E26	2 700	82	10 000	1 010	60	6/48
61030	CF15/T2/30K/SPIRAL/E26/ELUME	15	E26	3 000	82	10 000	1 010	60	6/48
61031	CF20/T2/27K/SPIRAL/E26/ELUME	20	E26	2 700	82	10 000	1 330	75	6/48
61032	CF23/T2/27K/SPIRAL/E26/ELUME	23	E26	2 700	82	10 000	1 600	100	6/48
61033	CF23/T2/30K/SPIRAL/E26/ELUME	23	E26	3 000	82	10 000	1 600	100	6/48
61034	CF23/T2/41K/SPIRAL/E26/ELUME	23	E26	4 100	82	10 000	1 600	100	6/48
61035	CF23/T2/50K/SPIRAL/E26/ELUME	23	E26	5 000	82	10 000	1 600	100	6/48

T2 Spirals packs

61022	CF13/T2/27K/SPIRAL/E26/ELUME 4P	13	E26	2 700	82	10 000	900	60	1/64
61025	CF13/T2/30K/SPIRAL/E26/ELUME 4P	13	E26	3 000	82	10 000	900	60	1/64
61027	CF13/T2/41K/SPIRAL/E26/ELUME 4P	13	E26	4 100	82	10 000	880	60	1/64
61028	CF13/T2/50K/SPIRAL/E26/ELUME 4P	13	E26	5 000	82	10 000	880	60	1/64
61023	CF13/T2/27K/SPIRAL/E26/ELUME 12P	13	E26	2 700	82	10 000	900	60	1/48

Starting temperature: -18 °C / 0 °F



2-pin Twin Tube




2-pin Double Twin Tube




4-pin Double Twin Tube




4-pin Triple Twin Tube




G23




GX23




G23-2



GX23-2




G24d-2




G24d-3




G24q-1



G24q-2



G24q-3



GX24q-3

2-pin

4-pin

Order code	Description	Watts (W)	Base	Colour temp. (K)	CRI	Life L70 (hrs)	Lumen output (lm)	MOL (in.)	MOL (mm)	Case qty (master)
2-pin Twin Tube										
14031	PL7/27K/TT/2P/ELUME	7	G-23	2 700	82	10 000	360	5 5/16	135	6/96
14035	PL13/27K/TT/2P/ELUME	13	GX-23	2 700	82	10 000	720	7 3/32	180	6/96
2-pin Double Twin Tube										
14106	PL9/27K/DTT/2P/ELUME	9	G23-2	2 700	82	10 000	475	4 11/32	110	6/96
14108	PL13/35K/DTT/2P/ELUME	13	GX23-2	3 500	82	10 000	810	4 21/32	118	6/96
14112	PL18/41K/DTT/2P/ELUME	18	G24d-2	4 100	82	10 000	1 035	5 31/32	152	6/96
14113	PL26/27K/DTT/2P/ELUME	26	G24d-3	2 700	82	10 000	1 540	6 13/16	173	6/96
14114	PL26/35K/DTT/2P/ELUME	26	G24d-3	3 500	82	10 000	1 540	6 13/16	173	6/96
4-pin Double Twin Tube										
14116	PL13/27K/DTT/4P/ELUME	13	G24q-1	2 700	82	10 000	810	5 5/32	131	6/96
14117	PL13/30K/DTT/4P/ELUME	13	G24q-1	3 000	82	10 000	810	5 5/32	131	6/96
14120	PL18/30K/DTT/4P/ELUME	18	G24q-2	3 000	82	10 000	1 035	5 25/32	147	6/96
14123	PL26/27K/DTT/4P/ELUME	26	G24q-3	2 700	82	10 000	1 540	6 1/2	165	6/96
14124	PL26/30K/DTT/4P/ELUME	26	G24q-3	3 000	82	10 000	1 540	6 1/2	165	6/96
4-pin Triple Twin Tube										
14130	PL32/30K/TTT/4P/ELUME	32	GX24q-3	3 000	82	10 000	2 160	5 25/32	147	6/96

