12	11	10 9	8 7	6		5	4	³ ORDER	NO. WOODHEAD	
									0082 24W47	YELLOW
									0082 24W47 0083 24W47BLK	BLACK
1								130140-	0003 24047 DLK	
										G
										E
	<u>FACE VIEW</u>		1.69 ►	3.55)						c
	DESCRIPTIONS	MATERIAL	QTY.	NOTEO	\ _					
	BLADES	BRASS	3	NOTES		ורדוראו פרוי		1301111770 -	OR PRODUCT SPE	
							2.375" TO 0.62		UN FRUDUUI SPE	
	RETAINING SCREWS		3							
3		BRASS, ZINC PLATED	3				CURRENT REV DESC: F	Y TO MOLEX ELECTRONIC TECH	HNOLOGIES, LLC AND SHOULD NOT BE USED	
4	INSERT	NYLON	1			INCH NTS			mole	ex 🗆
5	TERMINAL COVER	POLYCARBONATE	1			ENERAL TOLERANCES (UNLESS SPECIFIED)		-		
6	HOUSING	SILICONE WITH NYLON THREAD	1		P = 0 ANO	IGULAR TOL ± 0.5°	EC NO: 613699 DRWN: VHANDI	2019/03/13	WATERTITE PLUC	G, L5-15P
7	GROMMETS	RUBBER	5		$\boxed{\$} = 0 4P$ $\boxed{\$} = 0 3P$	· · · · · · · · · · · · · · · · · · ·	CHK'D: DNGUYEN6	2 2019/03/18		
A 8	FRICTION RING	NYLON	1		$\nabla = 0 \frac{31}{2P}$		APPR: HKNEELAN			R DRAWING
9	COMPRESSION NUT	NYLON	1		$\overrightarrow{P} = 0$	PLACE ± 0.02	DRWN: NVELUSAM	Y 2018/11/08	1301460082	PSD 000 A1
10	CABLE GLOVE	SILICONE	1			PLACES ± DRAFT WHERE APPLICABLE			MATERIAL NUMBER CUSTOMER	SHEET NUMBER
DOCUMENT ST	ATUS P1 RELEASE DATE	2019/03/21 15:00:54	I		☞= 0	MUST REMAIN WITHIN DIMENSIONS		-SIZE 130146	SEE TABLE GENERAL M	IARKET 1 OF 1
FORMAT: Itb-prod-C REVISION: H DATE: 2018/01/18	11	10 9	8 7	6		5	4	3	2	1