



Choose the right lamp for your application. STANDARD CFL are available in decorative shapes as well. They are suitable for outdoor\* applications (base up) and in enclosed\*\* fixtures. Operating temperatures: -23°C/-10°F to 55°C/131°F

A shape



Capsules



Order code	Description	Watts (W)	Base	Colour temp. (K)	CRI	Average life (hrs)	Initial lumens (lm)	Case qty	Incandescent equivalent (W)
<b>A Shape</b>		4 W: MOL : 4 1/8 in. (103 mm) 9 W: MOL : 4 7/8 in. (113 mm) 14 W and 16 W: MOL : 4 7/8 in. (124 mm)	Dia. : 2 7/8 in. (53 mm) Dia. : 2 7/8 in. (55 mm) Dia. : 2 7/8 in. (60 mm)						
58445	CF4/27K/A15/E26/STD	4	E26	2 700	82	8 000	225	25	25
58446	CF9/27K/A16/E26/STD */**	9	E26	2 700	82	8 000	470	40	40
58394	CF14/27K/A19/E26/STD */**	14	E26	2 700	82	8 000	800	60	60
<b>Capsules*</b>		15 W: MOL : 5 1/2 in. (140 mm) 20 W and 26 W: MOL : 6 3/8 in. (162 mm)	Dia. : 2 3/8 in. (60 mm) Dia. : 2 7/8 in. (73 mm)						
56268	CF15/27K/T19/E26/STD	15	E26	2 700	82	8 000	800	60	60
58395	CF15/30K/T19/E26/STD	15	E26	3 000	82	8 000	800	60	60
58396	CF15/41K/T19/E26/STD	15	E26	4 100	82	8 000	800	60	60
56269	CF15/50K/T19/E26/STD	15	E26	5 000	82	8 000	800	60	60
56270	CF20/27K/T19/E26/STD	20	E26	2 700	82	8 000	1 200	75	75
58400	CF20/30K/T19/E26/STD	20	E26	3 000	82	8 000	1 350	75	75
58401	CF20/41K/T19/E26/STD	20	E26	4 100	82	8 000	1 350	75	75
56271	CF20/50K/T19/E26/STD	20	E26	5 000	82	8 000	1 200	75	75
56272	CF26/27K/T23/E26/STD	26	E26	2 700	82	8 000	1 450	100	100
56273	CF26/50K/T23/E26/STD	26	E26	5 000	82	8 000	1 450	100	100

# Decorative Lamps



Candles



Globes



Order code	Description	Watts (W)	Base	Colour temp. (K)	CRI	Average life (hrs)	Initial lumens (lm)	Case qty	Incandescent equivalent (W)
<b>Candles</b>		3 W and 5 W: MOL : 4 1/2 in. (112 mm) 7 W and 9 W: MOL : 4 1/2 in. (122 mm)	Dia. : 1 1/2 in. (36 mm) Dia. : 1 7/8 in. (40 mm)						
58413	CF3/27K/CANDLE/E26/STD	3	E26	2 700	82	8 000	80	100	15
59841	CF5/T2/27K/CANDLE/E12/STD	5	E12	2 700	82	8 000	220	96	25
59842	CF5/T2/27K/CANDLE/E26/STD	5	E26	2 700	82	8 000	220	96	25
14167	CF7/27K/CANDLE/E12/STD	7	E12	2 700	82	8 000	350	96	30
14168	CF7/27K/CANDLE/E26/STD	7	E26	2 700	82	8 000	350	96	30
59843	CF9/T2/27K/CANDLE/E12/STD	9	E12	2 700	82	8 000	450	96	40
59844	CF9/T2/27K/CANDLE/E26/STD	9	E26	2 700	82	8 000	450	96	40
<b>Globes*</b>		9 W and 14 W: MOL : 4 1/2 in. (110 mm) 20 W and 25 W: MOL : 5 5/8 in. (143 mm)	Dia. : 2 1/2 in. (64 mm) Dia. : 3 3/4 in. (95 mm)						
58439	CF9/27K/G25/E26/STD */**	9	E26	2 700	82	8 000	495	48	40
58440	CF14/27K/G25/E26/STD */**	14	E26	2 700	82	8 000	850	48	40
61140	CF20/27K/G30/E26/STD	20	E26	2 700	82	8 000	1 100	48	60
57192	CF25/27K/G30/E26/STD	25	E26	2 700	82	8 000	1 300	48	60

