


Date: \_\_\_\_\_  
 In hands date of project: \_\_\_\_\_  
 Project name/Number: \_\_\_\_\_  
 Name of distributor: \_\_\_\_\_  
 Client #: \_\_\_\_\_  
 Name of end user: \_\_\_\_\_



MOL : 5 in. (127 mm)      Dia. : 4 <sup>23</sup>/<sub>32</sub> in. (120 mm)

## ORDERING INFORMATION

Order code: 63980  
 Description: LED/P38/15W/30K/40/STD  
 UPC: 69549639805  
 Case quantity: 6

## PERFORMANCE DATA

Shape: PAR38  
 Base: E26  
 Wattage (W): 15  
 Lamp voltage (VAC): 120  
 Colour temperature (K)\*\*: 3 000  
 Average life (L70 hours): 40 000  
 Initial lumens (lm)\*: 1 115  
 Initial lumens per watt (lm/W): 74  
 CRI: 94  
 R9: 67  
 Beam angle: 40  
 CBCP: 1 815  
 Power factor: 0.96  
 Operating temperature range: - 40 °C / - 40 °F to 40 °C / 104 °F

\*Initial lumens range: +/- 10 %      \*\*Typical colour temperature range: +/- 10 %



## CAUTIONS

- Turn power off before inspection, installation, or removal.
- Risk of electrical shock – do not use where directly exposed to water or weather.
- Not for use in totally enclosed luminaires.
- Suitable for use in damp locations.
- Do not open – no user serviceable parts inside.
- Added weight of the device may cause instability of a freestanding portable luminaire. Use in portable table lamps in which the distance from the bottom of the base to the top of the lamp holder does not exceed three (3) times the minimum base diameter.
- Use only on 120 VAC, 60Hz circuits.
- This device is not intended for use with emergency exit fixtures or emergency exit lights.
- Compatible with most dimmers.
- For complete dimmer and warranty information visit [www.standardpro.com](http://www.standardpro.com).
- Not recommended for use with timers.

Qty	Description	Price

I accept the specifications of the lamp configuration mentioned above.

Name: \_\_\_\_\_  
 Company: \_\_\_\_\_  
 Signature: \_\_\_\_\_

Date: \_\_\_\_\_

Data is based upon tests performed in a controlled environment and representative of relative performance. Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.

## COMPATIBLE DIMMER LIST

<b>Legrand</b>	H703PTUW, HCL453P
<b>Cooper</b>	DAL06P, SAL06P, SLC03P, AAL06
<b>Leviton</b>	IPL06, 6674, DSM10-1LZ
<b>Lutron</b>	DVCL-153P, CTCL-153P, MACL-153P, AYCL-253P, DVCL-253P, DVELV-300P, SELV-300P, NTELV-600