



TECHNICAL:
LISTED:
RATED SUPPLY VOLTAGE:
RATED CURRENT:
RESET TYPE:
OPERATING FREQUENCY:
TYPE:
GROUND TRIP CURRENT:
OVERLOAD CURRENT:
INSULATION VOLTAGE:
ENDURANCE OPERATIONS:

UL AND cUL
 120 VAC
 UP TO 15 AMPS OR CABLE RATING
 AUTOMATIC OR MANUAL
 60 Hz
 CLASS A
 4-6 mA
 90 AMP 125 VAC
 1,500 VRMS – 1 MINUTE
 3000 OPERATIONS

MATERIAL NO.	ENGINEERING NO.	LENGTH "L"	POWER-UP
1301530091	15054-1A	2 FT ± 1 IN	AUTO
1301530095	15054-25A	25 FT ± 2 IN	AUTO
1301530092	15054-1A	2 FT ± 1 IN	MANUAL
1301530096	15054-25M	25 FT ± 2 IN	MANUAL

INITIAL RELEASE EC NO.: IPG2013-1078 DRWN: HRUIZ01 2013/02/07 CH'KD: HKNEELAN 2014/07/22 APPR: JFMURPHY 2015/04/20	QUALITY SYMBOL ▽=0 ▽C=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE INCH		SCALE NTS	DESIGN UNITS INCH	THIRD ANGLE PROJECTION			
				mm	INCH	DRAWN BY	DATE	TITLE			
		4 PLACES	±---	±---	HRUIZ01	2013/02/07	120V 15A GFCI PLUG W/ MOLDED CONNECTOR NEMA 5-15				
		3 PLACES	±---	±.005	CHECKED BY	DATE					
2 PLACES	±0.13	±.010	HKNEELAN	2014/07/22	MOLEX INCORPORATED						
1 PLACE	±0.25	±.020	APPROVED BY	DATE							
		ANGULAR ±1/2°		JFMURPHY	2015/04/20	DOCUMENT NO. SD-130153-017					
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		MATERIAL NO. SEE TABLE		SHEET NO. 1 OF 1					
				SIZE C	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						