## **Technical Information Bulletin**

## **LED** Linear

Date:												
In hands date o	f project:					_						
Project name/N						_						
Name of distrib	-					_						
Client #:						_						
Name of end us	ser:					_	7					
ORDERING IN	NFORMAT	ION						Nominal length	ı : 48 in. (1 220 mn	n) Dia.:1 in.	. (26 mm)	
Order code:	65478							J				
Description:	LED/T8/S4/15W/840/48/STD											
UPC:	69549654785											
Case quantity:	25											
PERFORMAN	CE DATA											
Shape:	CL DAIA	Т8										
Base:		G13										
Starting metho	od:		nt, Rapid	l & Progra	m Start							
Lamp voltage (			/ - 277 V	_								
Color temperat		4 000										
Average life (L7	70 hours):	50 00	00									
CRI:		>80										
Beam angle (°):		>240										
Operating temp	perature ran		2 / -4°F to Standard	45°C / 113	3°F							
DLC Listed: *Initial lumens range: +/- 10	1 % **Typical co	Our temperature ran										
						ı						
Order code	Average System V	Vatts (W)	lni	tial Lumens (In	1)*							
	LBF NBF	HBF	LBF	NBF	HBF							
65478	16 18	26	1 800	2 100	2 850							
(H/g)	RMHS 5	الل) و	IIS									
DAMP NO MERCURY	COMPLIANT WARR	ANTY	03									
Please refer to the ballas	t compatibility list t	o confirm lamp o	ompatibility w	vith the existing	luminaire.							
CAUTIONS												
THIS LAMP OPERATES ON	N INSTANT START.	RAPID START AN	D MANY PRO	GRAM START	ELECTRONIC	C BALLASTS.						
Direct replacement for 25							re. Risk of	f electric shoc	k – for use in da	amp locations		
•	_											
Qty	ע	escription	1					Price				
I accept the spe	ecifications o	f the lamp o	configura	ition ment	ioned a	bove.						
		•	<b>J</b>									
Name:								_				
Company: _								_				

STANDARD\*

Date:

Signature: