


	12		11		10	9		
	PART NO.	E		Ю.	FINISHED LENGTH			
	1300130008	1F	R4006A20F040		4.0FT (1.2M)			
н	1300130353	1F	R4006A20A120		12.0IN (0.3M	V)		
	1300130918	1F	R4006A20M030		3M (9 FT, 1	0 IN)		







NOTES:

G

F

Е

D

С

В


- 1. MATERIAL: AS NOTED
- 2. FINISH: AS NOTED
- 3. ELECTRICAL: VOLTAGE: 483V PER IEC60664 600V PER UL2238

CURRENT: 10A

- 4. TEMP RATING: -20°C TO +105°C
- 5. PROTECTION: IP67 (WHEN MATED)
- 6. COUPLING THREAD: 7/8-16 UN
- 7. UL RECOGNIZED FILE: E152210
- CSA CERTIFIED: LR6837 8. ALL DIMS ARE FOR REFERENCE UNLESS TOLERANCED OR NOTED OTHERWISE

REF. KN	IOCKOL

	6	FLAG LABEI			VINYL	BLACK/YELLOW				
	5	POTTING M	ATE	RIAL	EPOXY					
	4	WIRE #16 (L	JL 1(015)	PVC INSU	SEE FACE VIEW				
	3	CONTACT F	PIN		Cu ALLO	GOLD PLATED YELLOW BLACK E-COAT				
	2	INSERT			TPE					
	1	RECEPTACI	LE S	HELL	ZINC (DIE					
	ITEM	DESCRIPTIO		MATERIA	FINISH					
DOCUMENT STATUS			P1	RELE	ASE DATE	2021/07/1	12 18:53:0	06		
FORMAT: Eng-lega-master-tb-prod-C REVISION: E DATE: 2020/1/4				1	1 1		10			



FL	
7	
4	
1	
DI S	

/= 0	(UNLE	ESS SPEC	IFIED)										
_		MM	INCH		000070			MINI-	CHANGE RECE	PTACLE			
/= 0	4 PLACES	±	±	EC NO:			0004/00/00	4 POLE MALE,	STRAIGHT, SIN	GLE KE	Y, 16 A	WG	
	3 PLACES	+	+	DRWN:	RSTONE		2021/06/23						
ISIONAL			-	CHK'D:	MZIELINSKI		2021/07/08						-
MBOLS	2 PLACES	±			PPR: BWOODMAN 2021/07/12				PRODUCT CUSTOMER DRAWING				Ι,
	1 PLACE	±	±	INITIAL	REVISION:			DOCUMENT NUMBER		DOC TYPE	DOC PART	REVISION	ſ
	0 PLACES	±	±	DRWN:	RSTONE		2021/06/23	130013	0000		000	٨	
	ANGULA	R TOL	±°	APPR:	BWOODMAN	l	2021/07/12	130013	0000	PSD	000	Α	
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANG	LE PROJECTION	DRAWING	SERIES	MATERIAL NUMBER	CUSTOMER		SHEET N	NUMBER]	
					C-SIZE	130013	SEE P/N LEGEND	GENERAL MA	RKET	1 C)F 1		