

Technical Information Bulletin

CHOICE LED Lamps



Date: _____ Name of distributor: _____
In hands date of project: _____ Client #: _____
Project name/Number: _____ Name of end user: _____

ORDERING INFORMATION


Order code: 66267
Description: A19/6W/27K/ND/CHOICE/STD
UPC: 69549662674
Case quantity: 6 / 48

PERFORMANCE DATA

Shape: A19
Base: E26
Watts(W): 6
Volts (VAC): 120
Colour temperature (K)**: 2 700
Life L70 (hrs): 15 000
Initial lumens (lm)*: 480
Initial lumens per watt (lm/W): 84
CRI: 81
Beam angle: 220
Power factor: 0.6
Operating temperature range: -20 °C to 45 °C (-4 °F to 113 °F)

*Initial lumens range: +/- 10 %

**Typical colour temperature range: +/- 5 %



CAUTIONS

- Turn power off before inspection, installation, or removal.
- Risk of electrical shock – do not use where directly exposed to water or weather.
- Suitable for use in totally enclosed luminaires.
- Suitable for use in damp locations.
- Do not open – no user serviceable parts inside.
- Use only on 120 VAC, 60Hz circuits.
- This device is not intended for use with emergency exit fixtures or emergency exit lights.
- Do not use with dimmers.
- For complete warranty information visit www.standardpro.com.
- 3 Years Limited Warranty.

Qty	Description	Price

I accept the specifications of the luminaire configuration mentioned above.

Name: _____
Company: _____
Signature: _____

Date: _____

This lighting equipment complies with Canadian standard ICES-005 for use in residential applications.
Data is based upon tests performed in a controlled environment and representative of relative performance.
Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.

June 18, 2020