Technical Information Bulletin





Date:	Name of distributor:	
In hands date of project:	Client #:	
Project name/Number:	Name of end user:	

ORDERING INFORMATION

Order code: 66272

Description: A19/9.5W/30K/ND/CHOICE/STD 4P

UPC: 69549662728 Case quantity: 12 x 4 pack

PERFORMANCE DATA

Shape: A19 4 pack

Base: E26 Watts(W): 9.5 Volts (VAC): 120 Colour temperature (K)**: 3 000 Average life (L70 hours): 15 000 Initial lumens (lm)*: 857 Initial lumens per watt (lm/W): 97 CRI: 82 Beam angle: 220

-20 °C to 45 °C (-4 °F to 113 °F) Operating temperature range:

0.6

*Initial lumens range: +/- 10 %



Power factor:




















This lighting equipment complies with Canadian standard ICES-005 for use in residential applications

CAUTIONS

- Turn power off before inspection, installation, or removal.
 Risk of electrical shock do not use where directly exposed to water or weather.
 Suitable for use in totally enclosed luminaires.
 Suitable for use in damp locations.
 Do not open no user serviceable parts inside.
 Use only on 120 VAC, 60Hz circuits.
 This device is not intended for use with emergency exit fixtures or emergency exit lights.
 Do not use with dimmers.
 For complete warranty information visit www.standardpro.com.
 3 Years Limited Warranty.

Qty	Description	Price	
I accept the spe	ecifications of the luminaire configuration mention	ned above.	
Name:			
Company:			
Signatura:		Date:	

This lighting equipment complies with Canadian standard ICES-005 for use in residential applications. Data is based upon tests performed in a controlled environment and representative of relative performance. Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.

