Technical Information Bulletin

CHOICE LED Lamps.



Date:	Name of distributor:	
In hands date of project:	Client #:	
Project name/Number:	Name of end user:	

ORDERING INFORMATION


Order code: 66302

Description: P38/16.5W/40K/40/CHOICE/STD

UPC: 69549663022

Case quantity: 6





Operating temperature range: -20 °C to 40 °C (-4 °F to 104 °F)

Traditional equivalent (W): 100

*Initial lumens range: +/- 10 % **Typical colour temp

**Typical colour temperature range: +/- 10 %

















MOL : 5 in. (127 mm) Dia. : 4 ³/₄ in. (120 mm)

COMPATIBLE DIMMERS

Legrand	HCL453P, RH703PTUTC	
Cooper	r AAL06, DAL06P, SLC03P	
Leviton	Leviton 6615, 6674, DSL06-1LZ, IPE04-1LZ, IPL06	
Lutron	AYCL-253P, CTCL-153P, DVCL-153P, DVCL-253P, DVELV-300P, MACL-153P, PD-6WCL, SELV-300P	

CAUTIONS

- Turn power off before inspection, installation, or removal.
- Not for use in totally enclosed luminaires.
- Suitable for use in wet locations.
- Do not open no user serviceable parts inside.
- Use only on 120 VAC, 60Hz circuits.
- This device is not intended for use with emergency exit fixtures or emergency exit lights.
- Compatible with most dimmers.
- For complete dimmer and warranty information visit www.standardpro.com.

Qty	Description	Pri	ice		
I accept the specifications of the luminaire configuration mentioned above.					
Name:					
Company:					
Signature:			Date:		

This lighting equipment complies with Canadian standard ICES-005 for use in residential applications. Data is based upon tests performed in a controlled environment and representative of relative performance. Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.