

Worklight

STANDARD's Worklights are ideal for projects where portable and temporary lighting is required, especially to provide a safe working environment when handling repairs, general maintenance or new construction. Find the perfect solution to illuminate your work area, whether it's for a wide area or to perform a specific task in a precise location.

STANDARD's temporary lighting products are made of robust material that are perfect for a rugged construction site where traditional lighting products would break easily.


115

String Light


STANDARD's String Lights come in lengths of 50 feet (15 m) and 100 feet (30 m) and are made of 12 or 14 AWG cable for heavy duty applications. As they can be daisy-chained, String Lights are ideal for jobsites where temporary lighting is needed for a wide area. Once the project is completed, they can be easily removed and transported to another location. Combine the String lights with STANDARD's wide range of LED A19 lamps.



| Order code | Description | Wi Len | ire gth | Wire | Maximum Watts per socket | | Amperage | Socket | Amount of sockets | Lamp guard material | Case qty |
|---------------|---|-----------|------------|----------------|--------------------------------|-----------------|------------|--------|-------------------------|---------------------------|-------------|
| | | (ff) | (m) | | (W) | (sockets) (stri | (A) Ig) | | | | (master) |
| 66850 | SL/50FT/DSC/5SKT/12AWG/PLASTIC/YL/STD | 50 | 15 | SJTW 12 AWG/3C | 150 | 120 12 | 5 12 | E26 | 5 | Plastic | 1 |
| 66851 | SL/100FT/DSC/10SKT/12AWG/PLASTIC/YL/STD | 100 | 30 | SJTW 12 AWG/3C | 150 | 120 12 | 5 12 | E26 | 10 | Plastic | 1 |
| 67770 | SL/100FT/DSC/10SKT/14AWG/PLASTIC/YL/STD | 100 | 30 | SJTW 14 AWG/3C | 150 | 120 12 | 5 12 | E26 | 10 | Plastic | 1 |



| | Order code | Description | Туре | Case qty (master) |
|---|---------------|------------------------|---------------------------|-------------------------|
| e | 66853 | SL/CAGE/PLASTIC/YL/STD | Plastic cage replacement | 50 |
| e | 66854 | SL/SHOOK/METAL/STD 5P | Metal S hooks (Pack of 5) | 1000 |





| Order code | Description | Colour temp. (K) | Lumen output (Im) | Dimming capability (Yes/No) | _ |
|---------------|-------------------------------|------------------------|-------------------------|-----------------------------------|---|
| 60 W E | quivalent | | | | |
| 66273 | A19/9.5W/40K/ND/CHOICE/STD 4P | 4 000 | 800 | No | |
| 66274 | A19/9.5W/50K/ND/CHOICE/STD 4P | 5 000 | 800 | No | |
| 75 W E | quivalent | | | | |
| 66186 | LED/A19/S4/11W/40K/STD | 4 000 | 1 196 | Yes | |
| 66187 | LED/A19/S4/11W/50K/STD | 5 000 | 1 178 | Yes | |
| 100 W | Equivalent | | | | |
| 66190 | LED/A19/S4/15W/40K/STD | 4 000 | 1 692 | Yes | |
| 66191 | LED/A19/S4/15W/50K/STD | 5 000 | 1 725 | Yes | |



¹ The recommended LED Lamps are suitable for damp location only.


60



Trouble Light

STANDARD's Trouble Light will provide direct lighting for a smaller and specific area. It can be hung using the hook, which leaves your hands free while performing a task. Multiple Trouble Lights can also easily be daisy-chained using the 25-foot (7.5 m) cable and the receptacle on the handle.

Combine the Trouble Light with STANDARD'S wide range of LED A19 lamps.



| Order code | Description | Wire I | ength | Wire | Maximum Watts per socket | Volts | Amperage | Socket | Lamp guard material | Case qty |
|---------------|----------------------------------|--------|-------|-----------|--------------------------------|-------|----------|--------|---------------------------|-------------|
| | | (ff) | (m) | | (W) | (V) | (A) | | | (master) |
| 66852 | 2 TL/25FT/DSC/16AWG/METAL/OR/STD | 25 | 7.5 | 16 AWG/3C | 75 | 120 | 10 | E26 | Metal | 12 |

Recommended Compatible LED Lamps¹

| Order code | Description | Colour temp. (K) | Lumen output (Im) | Dimming Capability (Yes/No) |
|---------------|----------------------------|------------------------|-------------------------|-----------------------------------|
| 60 W Eq | uivalent | | | |
| 66269 | A19/9.5W/27K/ND/CHOICE/STD | 2 700 | 800 | No |
| 66270 | A19/9.5W/30K/ND/CHOICE/STD | 3 000 | 800 | No |
| 66182 | LED/A19/S4/9.8W/40K/STD | 4 000 | 874 | Yes |
| 66183 | LED/A19/S4/9.8W/50K/STD | 5 000 | 585 | Yes |
| | | | | |







Temporary LED High Bay

Replacing traditional Metal Halide HID lamps and fixtures with our 150 W Temporary LED High Bay fixture is a cost saving and energy efficient solution. The Temporary High Bay provides 360° illumination and will ensure that the work area is safe and fully illuminated. Moreover, its high efficacy will help reduce the number of luminaires needed; in addition, the daisy chain feature will enable the use of one outlet to power up to four luminaires.

| Order code | Description | Watts (W) | Volts (V) | Colour temp. | Wire | CRI | Lumen output (Im) | Beam angle (°) | Life L70 (hrs) | Operating position | Case qty (master) |
|---------------|---------------------------|--------------|--------------|-----------------|------------|-----|-------------------------|----------------------|----------------------|-----------------------|-------------------------|
| 67046 | THB/DSC/150W/CW/ND/OR/STD | 150 | 120 | Cool White | 18AWG / 3C | 80 | 15 000 | 360 | 50 000 | Universal | 4 |



60



Luminaires - Worklight

Portable LED Flood Light


Portable Flood Lights are easy to carry from one location to another as they are battery powered and highly versatile. They offer pre-set intensities to disperse the right amount of light for each task and to ensure more efficient battery consumption. Their cordless feature keeps the ground free of cables, which creates a safer work environment. This product can be used on jobsites where electricity has yet to be installed.



| Order Description code | Watts | Volts | Colour Temp. | CRI | Light output | Beam angle | | m-ion tery | | orking time nrs) | Battery charging time | Case Qty |
|--|-------|---------|-----------------|-----|-----------------|---------------|-----|---------------|--------------------|-----------------------|-----------------------------|-------------|
| | (W) | (VAC) | | | (lm) | (°) | (V) | (Ah) | 100% Brightness | Energy saving mode | (hrs) | (master) |
| LED Mini Flood Light 67023 MFL/BTRY/MGN/100-240/10W/CW/BL/S | TD 10 | 100-240 | Cool White | 70 | 450 | 120 | 3.7 | 2.0 | 2 | 4 | 3 | 50 |

| Order Code | Description | Watts | Volts | Colour Temp. | CRI | Light output | Beam angle | | m-ion tery | Batte | ery working (hrs) | time | Battery charging time | Case qty |
|---------------|--------------------------------|-------|---------|-----------------|-----|-----------------|---------------|------|---------------|--------------------|----------------------|-------------------|-----------------------------|-------------|
| | | (W) | (VAC) | | | (lm) | (°) | (V) | (Ah) | 100% Brightness | 50% Brightness | 20% Brightness | (hrs) | (master) |
| LED | Flood Light | | | | | | | | | | | | | |
| 67021 | PFL/BTRY/100-240/20W/CW/YL/STD | 20 | 100-240 | Cool White | 70 | 1 100 | 120 | 7.4 | 4.4 | 3 | 6 | 12 | 5 | 8 |
| 67022 | PFL/BTRY/100-240/50W/CW/YL/STD | 50 | 100-240 | Cool White | 70 | 3 250 | 120 | 18.5 | 6.6 | 3 | 6 | 12 | 6 | 2 |

4"11/32 (110 mm) 1"5/16 (33 mm)











Flood 20 W



5 3/4" (146 mm)





Flood 50 W



65/32" (156 mm)



| Order Description code | Watts | | ım-ion ttery | Bat | tery Working (hrs) | lime | Battery charging | Compatible products | Case qty | |
|---|-------|-----|-----------------|--------------------|-----------------------|-------------------|---------------------|-------------------------|-------------|---|
| | (W) | (V) | (Ah) | 100% Brightness | 50% Brightness | 20% Brightness | time (hrs) | | (master) | 1 |
| Replacement Battery | | | | | | | | | | |
| 67024 ¹ PFL/REPLBTRY/7.4V/20W/YL/STD | 20 | 7.4 | 4.4 | 3 | 6 | 12 | 5 | 20 W LED Flood Liaht | 8 | |

| Order code | Description | | | Volts (VAC) | | Compatible products | Case qty (master) |
|---------------|----------------|---------|--------------|----------------|-----|------------------------|----------------------|
| Rep | lacement AC | C/DC Cł | narge | er | | | |
| 67026 | PFL/CHARGER/20 |)w/std | | 100-240 | 20 | W LED Flood Light | 25 |
| 67027 | PFL/CHARGER/50 | W/STD | | 100-240 | 50 | W LED Flood Light | 25 |
| Order code | Description | | imum ight | Maxim Heigh | | Compatible products | Case qty |
| | | (in) | (m) | (in) | (m) | | (master) |

0.66

61 31/32" (1574 mm)

26.7



1

Tripod

67025 PFL/TRIPOD/YL/STD 62 1.56 20 W LED Flood Lights (3 units) 50 W LED Flood Lights (2 units)

19 1/16" (484 mm)






STANDARD* © 2019 STANDARD Products Inc. All Rights Reserved. www.standardpro.com Rev. September 25, 2019 .

AC Flood Light

STANDARD's AC Flood Lights of 30 W and 50 W are the perfect combination of durability and efficiency. Offering a high light output and designed for wet locations, with an IP rating of 65, these luminaires will suit the most robust construction sites. Magnetic feet are also available as accessories, allowing the AC Flood Lights to stick to any metallic surface. In addition, up-to three Flood Light can be installed on the tripod.



| Order code | Description | Watts | Volts | Colour temp. | Wire | CRI | Light output | Beam angle | Life L70 | Case qty |
|---------------|-------------------------|-------|-------|-----------------|--------|-----|-----------------|---------------|-------------|-------------|
| | | (W) | (VAC) | | | | (lm) | (°) | (h) | (master) |
| 67336 | PFL/AC/30W/CW/ND/YL/STD | 30 | 120 | Cool White | 18 AWG | 70 | 3 200 | 120 | 25 000 | 8 |
| 67337 | PFL/AC/50W/CW/ND/YL/STD | 50 | 120 | Cool White | 18 AWG | 70 | 5 100 | 120 | 25 000 | 8 |



| Acc | Accessory | | | | | | | | | | |
|---------------|-------------------------|----------------|---------------------------------|----------------------------|-------------------------|---|--|--|--|--|--|
| Order code | Description | Туре | Compatible products | Qty per pack (units) | Case qty (master) | | | | | | |
| 67338 | PFL/AC/MAGNETICFEET/STD | Magnetic feets | AC Flood Lights - 30 W and 50 W | 4 | 100 | P | | | | | |

