THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP. 0.750 NO WARRANTY, EXPRESSED OR IMPLIED, IS MADE BY PANDUIT WITH [19.0] RESPECT TO ADHESIVE BOND PERFORMANCE. AMONG OTHER THINGS, THE CONDITIONS UNDER WHICH THESE MOUNTS MAY BE APPLIED AND/OR THE SURFACE TO WHICH THEY MAY BE APPLIED ARE BEYOND PANDUIT'S CONTROL. USE WITH THESE WEIGHT PANDUIT CABLE TIE lbs (g)/100 pcs PART NO. 0.750 CROSS SECTIONS [19.0] MINIATURE 0.113 ABMM - AT INTERMEDIATE (51.3)TO APPLY MOUNT 1) CLEAN SURFACE WITH ISOPROPYL ALCOHOL. 2) REMOVE PROTECTIVE LINER. 3) PLACE IN DESIRED LOCATION. 4) APPLY PRESSURE TO MOUNT FOR 5 SECONDS. NOTES: 0.171 ± 0.020 [4.39±.508] * 1) SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE AND PART COLOR. 2) MOUNTS ARE SUPPLIED IN STRIPS OF TWO FOR 0.180 EASY REMOVAL OF LINER. [4.6] 3) MOUNT HAS A CONTINUOUS OPERATING (REF) TEMPERATURE OF 180°F(82°C). ADHESIVE TAPE $0.065 \pm .010$ PRESSURE SENSITIVE TAPE 0.040(1.0) [1.57±.254] THICK WITH PROTECTIVE LINER. MOUNT IS DESIGNED TO SUPPORT 0.30 16s(136 g)
MAX. WEIGHT ON A CLEAN, DRY, SMOOTH, ACTUAL SIZE GREASE-FREE SURFACE. (DIMENSIONS IN PARENTHESES ARE IN METRIC.) CAD FILENAME/LAYERS G00239ER_DC_ABMM_AT_08 TINLEY PARK, ILLINOIS ABMM - AT ADHESIVE BACKED MOUNT UNLESS OTHERWISE SPECIFIED. UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCES ARE: ALL DIMENSIONS ARE GIVEN $(.x) \pm --- (.xxx) \pm .020(.51)$ IN INCHES, THIRD ANGLE PROJECTION. (.XX) ± .02(.5) ANGLES ± ----DRAWN BY MAT'L: NONE ABS DRAWING NO. DWG 8 (ACRYLONITRILE BUTADIENE STYRENE) l6/29/06 l JAD REMOVE ABM20B GB0239ER 12-23-96 CHK 'D GB0239ER DATE BY СНК DESCRIPTION ECN - R CUST SUP SIZE