	2							1						
	Τł	HIS CO	PY IS	5 PRO'	VIDED	ON A RESTRICTED BAS	IS AND IS NOT TO BE US	SED IN ANY W	'AY DETRIME	ental t	O THE I	INTERESTS (OF PANDUIT CORP.	
										PAN	PANDUIT PART NO		WEIGHT	
											WMPVS	MK	0.3 LBS/EAC 0.14 Kg/EAC	H H
										NOT	ES:			
В										2.	WWW.P/ CURREN USE W DIMENS METRIC COMPON 4-3/ 4-3/ 4-3/	ANDUIT.C NT PARTS ITH THIS SIONS IN C. NENTS: /8" FLAT /8-16 X /8-16 HE	1" BOLT	
<u> </u>)								
A									TITLE	N		NER SIDE I (WMPVSM stomer dra		A
									ITEM REVISION NA	00150	INBD/00	STUMEN DRA		
									DATASET FILE NAME 00150NBD_DC/00A UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOL			. TOLERANCES ARE:		
												ANGLE +/- 1°	STEEL	
00.	A 9	9–16–16	тwv	JEFK	KRKE	RELEASED TO PRODUCTION		00150NBD-DC		$-\bigcirc$	THI	RD ANGLE DJECTION	drawing number: 00150NBD-	- DC
RE	EV [DATE	ΒY	СНК	APR	DESCR	RIPTION	ECN	DRAWN BY DATE	-16-16	CHK S	SCALE NONE	SHT 1 0F 1	SIZE
						2			· · ·		· · · · · · · · · · · · · · · · · · ·	1		