



Quality Products. Service Excellence.

Four Post Fixed Depth Shelf *RF Series*

350 lbs (159 kg) Weight Capacity

Features



- Constructed of heavy-duty 14 gauge steel.
- Front & rear lip folded for extra strength.
- The versatile design can be used upside down (front & rear lip become equipment retainers).
- Sides folded up for easy hardware installation from above.
- Sides are slotted for easy adjustment with most rail depth locations.
- Includes all mounting hardware.
- Tested to nearly double the suggested load rating of 350 lbs (159 kg).
- Finished in textured RAL9005 black powder paint.
- TAA-compliant for GSA Schedule purchases.
- RoHS and REACH compliant.
- Manufactured in North America.



Please note that to mount this product you need to have two (2) pairs of combination rails within your cabinet. This product does not mount to the front and back of the rails like traditional rack mounting shelves.



If used with our CPR square hole rails you will need to order CPRSA rail adaptor for each shelf ordered.

Accessories

- Fixed Shelf Rail Adapter
- Square Hole Mounting Rail Adaptor
- Hook and Loop Roll



Solid Part No.	Vented Part No.	Height	Flange Location	Overall Dimensions		
				Height	Width	Depth
RFUS1918BK1	RFVS1918BK1	0.81	Front and Rear	1.94	17.75	18.00
RFUS1921BK1	RFVS1921BK1	0.81	Front and Rear	1.94	17.75	21.00
RFUS1926BK1	RFVS1926BK1	0.81	Front and Rear	1.94	17.75	26.00
RFUS1931BK1	RFVS1931BK1	0.81	Front and Rear	1.94	17.75	31.00

© 2021. Hammond Manufacturing Ltd. All rights reserved.