

PILOT LIGHT

1783.08 mm
[70.200 in]

265.62 mm
[10.458 in]

76.20 mm TYP
[3.000 in]

27.05 mm TYP
[1.065 in]

41.05 mm
[1.616 in]

SECTION A-A
(VIEW FROM FRONT)

RESETTABLE
CIRCUIT
BREAKER

6' FOOT
POWER CORD
(NEMA 5-15P)

29.18 mm
[1.149 in]

5.08 mm
[0.200 in]

ASSEMBLY - VIEW FROM END

1789.89 mm
[70.468 in]

ASSEMBLY - VIEW FROM SIDE



ISOMETRIC VIEW

1587T19A1

- Finish - Case - Anodized Aluminum Extrusion
- Ends - ABS Plastic
- Rated - 125 VAC, 60 Hz, 15 Amps
- Approvals - CSA Certified Standards C22.2 (No. 21-95, 42-99)
- UL Listed Standard UL1363

Accessories Included

- Mounting Bracket Kit with Hardware



**HAMMOND
MANUFACTURING™**

1587T19A1

www.hammondmfg.com