

Quality Products. Service Excellence.

Type 4 Mild Steel Two Door Floormount Enclosure 1422 N4 FM Series

Continuous Hinge Door with Clamps



Inner Panel Included









Application

- Designed to house electrical, electronic, hydraulic or pneumatic controls and instruments.
- Provides protection where equipment may be hosed down or otherwise be very wet, or in outdoor applications for full weather protection.

Standards

- UL 508A Type 3R, 4 and 12
- CSA Type 3R, 4 and 12
- · Complies with
 - o NEMA Type 3R, 4 12 and 13
 - o IEC 60529, IP66

Construction

- Enclosures are formed steel 12 gauge (60" high) or combination 10/12 gauge (72" high)
- Smooth, continuously welded seams without knockouts, cutouts or holes.
- Body stiffeners are provided in the larger enclosures for extra rigidity.
- Heavy duty lifting eyebolts are provided with reinforcing support angles.
- · Center post is removable for easy installation of the inner panel.
- Formed lip on door and top of enclosure opening exclude flowing liquids and contaminants.
- Continuously hinged doors may be removed by pulling the stainless steel hinge pin.
- · Doors are secured with heavy duty stainless steel clamps.
- · Provision for padlocking.
- 12" floor stands are welded to the enclosure.
- · Seamless poured-in place gasket.
- · Provision for light kit mounting.
- A removable 10 gauge inner panel is included.
- Panel supports are provided for easy panel installation.
- · Collar studs are provided for mounting inner panels.
- A bonding stud is provided on the door and a grounding stud is provided in the enclosure for each door.
- A literature pocket is provided for the inside of the door.

Finish

- Cover and enclosure are finished in recoatable smooth ANSI 61 gray powder coating.
- · Removable white inner panel is finished in white powder coating.

Accessories

- Additional Inner Panels
- Barrier Kits for Type 4 Floormount
- Enclosure Stabilizers
- Window Kits
- General Accessories

- · Door Stop Kit
- Drip Shield Kit
- Climate Control
- Lighting

New and improved PDF part drawing files with more detail now available.

Click part number in table below to access PDF, DXF, and STEP files.

w/ Feet		Enclosure			Panel	
Part No.	Н	W	D	н	W	
1422N4B10F	60.13	48.06	10.69	56.00	44.00	
1422N4D12F	60.13	60.06	12.69	56.00	56.00	
1422N4E12F	72.13	60.06	12.69	68.00	56.00	
1422N4F12F	72.13	72.06	12.69	68.00	68.00	
1422N4F24F	72.13	72.06	24.69	68.00	68.00	

Data subject to change without notice

© 2021. Hammond Manufacturing Ltd. All rights reserved.