

Project Name

Location

Prepared By



## SATCO S8778

20WA21/LED/4K/120V/DIM/E26

### Notes

[www] 06-27-2021 00:19:13

### General

Status	Active
Watts	20W
Incandescent Equivalent	150W
Volts	120V
Shape	A21
Base	Medium
ANSI Base	E26
Finish	Frost
CCT (Kelvin)	4000
Temperature	Cool White
CRI	80+
Lumens	2747L
Beam Spread	280
Dimmable	Yes-Dimmable
Hours Rated	25000
Lamp Type	Type A
Technology	LED
Min Compartment Size	Length: 8.50 in. Width: 6 in. Depth: 6 in.

### Electrical

Candlepower	266
Dimming Type	Forward Phase or Reverse Phase or Phase Selectable
Power Factor	>0.9
Burning Position	Universal
Operating Temperature	-25C (-13F) to a maximum of +45C (+113F)

### Physical

MOL	5
MOD	2.63
Lens Finish	Frost

### Additional Information

Rated For Enclosed Fixture	Yes
Warranty	5 Year Limited - Hi-Pro

### Compliance

Safety Listing	cULus
Location Rating	Damp
Energy Star	Yes
ES Unique ID	ESID-2321959
California Status	Lawful for sale
RoHS Compliant	Yes
FCC Compliant	Yes
SDS Sheet	LED_Lamp