SATCO' NUVO

Project Name

Location

Prepared By



15.5A19/LED/30K/ND/120V/4PK

Notes

General Status Active Watts 15.5W 100W Incandescent Equivalent Volts 120V Shape A19 Base Medium ANSI Base E26 Finish Frost CCT (Kelvin) 3000 Temperature Warm White CRI 90+ Lumens 1490L Beam Spread 220 Dimmable Non-Dimmable Hours Rated 15000 Lamp Type Type A Technology LED Electrical -20C (-4F) to a maximum of +45C **Operating Temperature** (+113F) Physical MOL 4.63 MOD 2.38 Housing Color White Additional Information Additional Info Rough Service; Vibration Service Rated For Enclosed Fixture Yes Warranty 3 Year Limited Compliance cULus Safety Listing Location Rating Damp No Energy Star California Status Lawful for sale **RoHS** Compliant Yes SDS Sheet LED_Lamp

For More Information Visit: <u>http://www.satco.com/</u>

