

Project Name

Location

Prepared By



SATCO S29915

14T8/LED/48-840/BP 120-277V

Notes

[www] 10-11-2021 02:00:31

General

Status	Discontinued
Substitute	S39915
Watts	14W
Fluorescent Equivalent	25W-32W
Volts	120V-277V
Ballast Type	Type B
Shape	T8
Base	Medium Bi Pin
ANSI Base	G13
Nominal Length	48
Finish	Frost
CCT (Kelvin)	4000
Temperature	Cool White
CRI	82
Lumens	1800L
Beam Spread	210
Dimmable	Non-Dimmable
Hours Rated	50000
Lamp Type	Linear
Technology	LED

Electrical

Ballasting Requirements	Ballast Bypass
Power Factor	0.9
Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)

Physical

MOL	48
MOD	1
Lens Finish	Frost

Additional Information

Additional Info	All glass tube
Tube Guard Use	Approved for use with tube guards
Installation Notes	Existing wiring to both sockets can remain in place. Will work on both shunted or non-shunted sockets.
Specification Note	Built-in shock resistant circuit - (not hot until both ends are installed)
Warranty	5 Year Limited - T8 LED Bulbs - Ballast Bypass

Compliance

Safety Listing	cULus Classified
Location Rating	Damp
Energy Star	No
DLC Approved	Yes
DLC ID	PLBVGJNTAU69
California Status	Lawful for sale
RoHS Compliant	Yes
FCC Compliant	Yes
NSF Approved	Yes

