SATCO' NUVO

Project Name

Location

Prepared By



SATCO S16411

36T8/LED/HO-SIGN/96-865/BP

Notes

General Status Active 36W Watts Fluorescent Equivalent 113W Volts 120V-277V Ballast Type Туре В Shape Τ8 **Recessed Double Contact** Base HO/VHO R17d ANSI Base 96 Nominal Length Finish Frost CCT (Kelvin) 6500 Temperature Daylight CRI 83 Lumens 5000L Beam Spread 360 Dimmable Non-Dimmable Hours Rated 50000 Lamp Type Linear Technology LED Electrical **Ballasting Requirements Ballast Bypass Operating Frequency** 50/60 Hz Power Factor 0.9 -30C (-22F) to a maximum of +45C **Operating Temperature** (+113F) Physical MOL 93.88 MOD 1 Material Plastic Lens Finish Frost Additional Information No ballast or external driver Installation Notes required; Direct wire 120-277V line voltage; Single ended wiring 5 Year Limited - T8 LED Bulbs -Warranty Ballast Bypass - Outdoor Sign Compliance Safety Listing cULus Classified Location Rating Damp Energy Star No California Status Lawful for sale **RoHS** Compliant Yes FCC Compliant Yes NSF Approved Yes

For More Information Visit: <u>http://www.satco.com/</u>

