SATCO" NUVO

Project Name

Prepared By



SATCO S39394 54W/LED/HID/5K/100-277V/EX39

Notes

General Status Active Watts 54W Incandescent Equivalent 300W Fluorescent Equivalent 85W HID Equivalent 250W Volts 100V-277V Shape Corncob Base Mogul Extended ANSI Base EX39 Finish Clear CCT (Kelvin) 5000 Temperature Natural Light CRI 80 7722L Lumens Beam Spread 300 Dimmable Non-Dimmable Hours Rated 50000 Lamp Type Corncob Technology LED Length: 15.75 in. Width: 8 in. Min Compartment Size Depth: 8 in. Ballast Bypass- Direct wire only Ballasting Requirements 100V-277V Electrical

| Working Voltage | AC 100-277V |
|-----------------------|--|
| Operating Frequency | 50/60 Hz |
| Power Factor | >0.9 |
| Burning Position | Up or Down Operation Only |
| Surge Protection | Built-in surge protection - 4KV |
| Operating Temperature | -25C (-13F) to a maximum of +45C (+113F) |

| Physical | |
|----------------------------|--|
| MOL | 9.03 |
| MOD | 3.34 |
| Lens Finish | Plastic (PS) |
| Lens Material | Plastic (PS) |
| Housing Color | White |
| Weight (lb.) | 1.89 |
| Additional Information | |
| Additional Info | Approved for totally enclosed fixtures; Base up or base down operation; For outdoor & indoor use; Emits no UV light / Contains no Mercury (Hg) |
| Rated For Enclosed Fixture | Yes |
| IP Rating | IP64 |
| Shatter-Proof Type | Shatter resistant materials. Acceptable for use in food prep areas |
| Warranty | 5 Year Limited - Hi-Pro |
| Compliance | |

| Safety Listing | cULus |
|-------------------|-----------------|
| Location Rating | Damp |
| Energy Star | No |
| DLC Approved | Yes |
| DLC ID | PLXDJHRLRK97 |
| California Status | Lawful for sale |
| RoHS Compliant | Yes |
| FCC Compliant | Yes |
| SDS Sheet | LED_Lamp |

Copyright 2020 Satco Products, Inc. All Rights Reserved

For More Information Visit: <u>http://www.satco.com/</u>

