SATCO' NUVO

Project Name

Location

Prepared By



SATCO S39397 120W/LED/HID/5K/100-277V/EX39

Notes

[www] 11-22-2021 02:57:43

Status	Active
Watts	120W
Incandescent Equivalent	750W
Fluorescent Equivalent	200W
HID Equivalent	600W
Volts	100V-277V
Shape	Corncob
Base	Mogul Extended
ANSI Base	EX39
Finish	Clear
CCT (Kelvin)	5000
Temperature	Natural Light
CRI	80
Lumens	17160L
Beam Spread	300
Dimmable	Non-Dimmable
Hours Rated	50000
Lamp Type	Corncob
Technology	LED
Min Compartment Size	Length: 17.32 in. Width: 9.25 in. Depth: 9.25 in.
Ballasting Requirements	Ballast Bypass- Direct wire only 100V-277V
Electrical	
Working Voltage	AC 100-277V
Operating Frequency	50/60 Hz
Power Factor	>0.9
Burning Position	Up or Down Operation Only
Surge Protection	Built-in surge protection - 6KV
Thermal Management	Hi-PRO lamps are manufactured with a new Thermal Management circuit design (Temperature Control).I
Operating Temperature	-25C (-13F) to a maximum of +45C (+113F)
Physical	
MOL	10.34
MOD	4.72
Lens Finish	Plastic (PS)
Lens Material	Plastic (PS)
Housing Color	White
Weight (lb.)	3.69
Additional Information	
Additional Info	Approved for totally enclosed fixtures; Base up or base down operation; For outdoor & indoor use; Emits no UV light / Contains no Mercury (Hg)
Rated For Enclosed Fixture	Yes
IP Rating	IP64
Shatter-Proof Type	Shatter resistant materials. Acceptable for use in food prep

Warranty	areas 5 Year Limited - Hi-Pro
Safety Listing	
Location Rating	Damp
Energy Star	No
DLC Approved	Yes
DLC ID	PLZWRGQMT164
California Status	Lawful for sale
RoHS Compliant	Yes
FCC Compliant	Yes
SDS Sheet	LED_Lamp

Copyright 2020 Satco Products, Inc. All Rights Reserved

For More Information Visit: <u>http://www.satco.com/</u>

