

Project Name

Location

Prepared By



## SATCO S39671

22W/LED/HID/2700K/100-277V E26

### Notes

[www] 11-22-2021 02:57:43

### General

Status	Active
Watts	22W
Incandescent Equivalent	150W
Fluorescent Equivalent	40W
HID Equivalent	100W
Volts	100V-277V
Shape	Corn cob
Base	Medium
ANSI Base	E26
Finish	Clear
CCT (Kelvin)	2700
Temperature	Warm White
CRI	80
Lumens	2860L
Beam Spread	300
Dimmable	Non-Dimmable
Hours Rated	50000
Lamp Type	Corn cob
Technology	LED
Min Compartment Size	Length: 8.5 in. Width: 6 in. Depth: 6 in.
Ballasting Requirements	Ballast Bypass- Direct wire only 100V-277V

### Electrical

Working Voltage	AC 90-305V
Operating Frequency	50/60 Hz
Power Factor	>0.9
Burning Position	Universal
Surge Protection	Built-in surge protection - 2.5KV
Operating Temperature	-25C (-13F) to a maximum of +45C (+113F)

### Physical

MOL	5.94
MOD	2.38
Lens Finish	Plastic (PS)
Lens Material	Plastic (PS)
Housing Color	White
Weight (lb.)	0.68

### Additional Information

Additional Info	UL approved for totally enclosed fixtures; For outdoor & indoor use; Emits no UV light / Contains no Mercury (Hg)
Rated For Enclosed Fixture	Yes
IP Rating	IP64
Shatter-Proof Type	Shatter resistant materials. Acceptable for use in food prep areas
Warranty	5 Year Limited - Hi-Pro

### Compliance

Safety Listing	cULus
Location Rating	Damp
Energy Star	No
California Status	Lawful for sale
RoHS Compliant	Yes
FCC Compliant	Yes
SDS Sheet	LED_Lamp

Copyright 2020 Satco Products, Inc.  
All Rights Reserved

For More Information Visit:  
<http://www.satco.com/>

