

Project Name

Location

Prepared By



# SATCO S12214

8.9PAR30L/LED/830/FL/120V

Notes

[www] 11-22-2021 02:57:41

## General

Status	Discontinued
Substitute	S22214
Watts	8.9W
Incandescent Equivalent	75W
Volts	120V
Shape	PAR30LN
Base	Medium
ANSI Base	E26
Finish	Clear
CCT (Kelvin)	3000
Temperature	Soft White
CRI	80
Lumens	700L
Beam Spread	40
Dimmable	Yes-Dimmable
Hours Rated	11000
Lamp Type	PAR
Technology	LED

## Electrical

Operating Frequency	60 Hz
CBCP	1315
Spot Type	FL - Flood
Dimming Type	Forward Phase or Reverse Phase
Power Factor	0.7
Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)

## Physical

MOL	4.41
MOD	3.75
Lensed	Lensed Lamp
Lens Finish	Plastic (PS)
Lens Material	Plastic (PS)
Housing Color	White

## Additional Information

Rated For Enclosed Fixture	Yes
Warranty	3 Year Limited

## Compliance

Safety Listing	cULus
Location Rating	Wet
Energy Star	No
California Status	Non-Compliant
RoHS Compliant	Yes
FCC Compliant	Yes
SDS Sheet	LED_Lamp