

Project Name

Location

Prepared By



SATCO S39977

15T8/LED/48-840/DR

Notes

[www] 10-11-2021 02:00:30

General

Status	Discontinued
Substitute	S49977
Watts	15W
Fluorescent Equivalent	25W-32W
Ballast Type	Type A
Shape	T8
Base	Medium Bi Pin
ANSI Base	G13
Nominal Length	48
Finish	Gloss White
CCT (Kelvin)	4000
Temperature	Cool White
CRI	82
Lumens	2200L
Beam Spread	210
Dimmable	Yes-Dimmable
Hours Rated	50000
Lamp Type	Linear
Technology	LED

Electrical

Ballasting Requirements	Ballast required. Direct Replacement-for use on Instant Start and Rapid Start ballasts with no rewiring required. May not be compatible with every ballast. Refer to the ballast compatibility chart
Power Factor	0.9
Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)

Physical

MOL	48
MOD	1
Lens Finish	Gloss White

Additional Information

Warranty	5 Year Limited - T8 LED Bulbs
----------	-------------------------------

Compliance

Safety Listing	cULus
Location Rating	Damp
Energy Star	No
DLC Approved	Yes
DLC ID	PL3A7LM1DMBQ
California Status	Lawful for sale
RoHS Compliant	Yes
FCC Compliant	Yes
NSF Approved	Yes

