

Project Name

Location

Prepared By



SATCO S21743

6.5MR16/LED/3K/40D/GU10/2PK

Notes

[www] 05-27-2021 00:19:11

General

Status	Active
Watts	6.5W
Incandescent Equivalent	50W
Volts	120V
Shape	MR16
Base	Bi Pin GU10
ANSI Base	GU10
Finish	White
CCT (Kelvin)	3000
Temperature	Warm White
CRI	80
Lumens	500L
Beam Spread	40
Dimmable	Yes-Dimmable
Hours Rated	25000
Lamp Type	MR
Technology	LED

Electrical

CBCP	750
Dimming Type	Forward Phase or Reverse Phase or Phase Selectable
Power Factor	0.7
Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)

Physical

MOL	2.20
MOD	1.97
Lensed	Lensed Lamp
Lens Finish	Clear
Housing Color	White

Additional Information

Rated For Enclosed Fixture	Yes
Warranty	3 Year Limited

Compliance

Safety Listing	cULus
Location Rating	Damp
Energy Star	Yes
ES Unique ID	ESID-2348474
California Status	Non-Compliant
California Compliant Substitute	S9383
RoHS Compliant	Yes
FCC Compliant	Yes
SDS Sheet	LED_Lamp