

Project Name

Location

Prepared By



## SATCO S11402

5.8A19/LED/27K/120V/ECO/ND

### Notes

[www] 06-09-2021 01:41:21

### General

Status	Active
Watts	5.8W
Incandescent Equivalent	40W
Volts	120V
Shape	A19
Base	Medium
ANSI Base	E26
Finish	White
CCT (Kelvin)	2700
Temperature	Warm White
CRI	80
Lumens	450L
Beam Spread	220
Dimmable	Non-Dimmable
Hours Rated	10000
Lamp Type	Type A
Technology	LED

### Electrical

Operating Frequency	60 Hz
Power Factor	0.55
Operating Temperature	-25C (-13F) to a maximum of +45C (+113F)

### Physical

MOL	4.34
MOD	2.38
Housing Color	White

### Additional Information

Rated For Enclosed Fixture	Yes
Warranty	3 Year Limited

### Compliance

Safety Listing	cULus
Location Rating	Damp
Energy Star	No
California Status	Non-Compliant
RoHS Compliant	Yes
SDS Sheet	LED_Lamp