

Project Name

Location

Prepared By



# SATCO S11414

9.5A19/LED/827/120V/D/4PK

**Notes**

[www] 10-25-2021 04:00:40

**General**

Status	Active
Watts	9.5W
Incandescent Equivalent	60W
Volts	120V
Shape	A19
Base	Medium
ANSI Base	E26
Finish	Frost
CCT (Kelvin)	2700
Temperature	Warm White
CRI	80
Lumens	800L
Beam Spread	230
Dimmable	Yes-Dimmable
Hours Rated	15000
Lamp Type	Type A
Technology	LED

**Electrical**

Operating Frequency	60 Hz
Dimming Type	Forward Phase or Reverse Phase or Phase Selectable
Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)

**Physical**

MOL	4.17
MOD	2.38
Weight (lb.)	0.08

**Additional Information**

Rated For Enclosed Fixture	Yes
Warranty	3 Year Limited

**Compliance**

Safety Listing	cULus Listed
Location Rating	Damp
Energy Star	No
California Status	Non-Compliant
RoHS Compliant	Yes
SDS Sheet	LED_Lamp