## SATCO' NUVO

Project Name

Location

Prepared By



SATCO S11423

15.5A19/LED/830/120V/D/4PK

Notes

General Status Active Watts 15.5W 100W Incandescent Equivalent Volts 120V Shape A19 Base Medium ANSI Base E26 Finish Frost CCT (Kelvin) 3000 Temperature Soft White CRI 80 Lumens 1600L Beam Spread 230 Yes-Dimmable Dimmable Hours Rated 15000 Lamp Type Type A Technology LED Electrical **Operating Frequency** 60 Hz Forward Phase Dimming Type -20C (-4F) to a maximum of +45C **Operating Temperature** (+113F) Physical MOL 4.57 MOD 2.38 Weight (lb.) 0.14 Additional Information Rated For Enclosed Fixture Yes Warranty 3 Year Limited Compliance Safety Listing cULus Listed Location Rating Damp Energy Star No California Status Non-Compliant **RoHS** Compliant Yes SDS Sheet LED\_Lamp



For More Information Visit: <u>http://www.satco.com/</u>

