SATCO NUVO

Project Name

Prepared By



Maria			
Notes			

Status	Active
Watts	15.5W
Incandescent Equivalent	100W
Volts	120V
Shape	A19
Base	Medium
ANSI Base	E26
Finish	Frost
CCT (Kelvin)	4000
Temperature	Cool White
CRI	80
Lumens	1600L
Beam Spread	230
Dimmable	Yes-Dimmable
Hours Rated	15000
Lamp Type	Type A
Technology	LED
Electrical	
Operating Frequency	60 Hz
Disconsiss or Turns	Famuard Dhaga

Electrical				
Operating Frequency	60 Hz			
Dimming Type	Forward Phase			
Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)			

Physical	
MOL	4.57
MOD	2.38
Weight (lb.)	0.14

Additional Information	
Rated For Enclosed Fixture	Yes
Warranty	3 Year Limited

Compliance			
Safety Listing	cULus Listed		
Location Rating	Damp		
Energy Star	No		
California Status	Non-Compliant		
RoHS Compliant	Yes		
SDS Sheet	LED_Lamp		





