

Project Name

Location

Prepared By



SATCO S11425

15.5A19/LED/850/120V/D/4PK

Notes

[www] 10-25-2021 04:00:40

General

Status	Active
Watts	15.5W
Incandescent Equivalent	100W
Volts	120V
Shape	A19
Base	Medium
ANSI Base	E26
Finish	Frost
CCT (Kelvin)	5000
Temperature	Natural Light
CRI	80
Lumens	1600L
Beam Spread	230
Dimmable	Yes-Dimmable
Hours Rated	15000
Lamp Type	Type A
Technology	LED

Electrical

Operating Frequency	60 Hz
Dimming Type	Forward Phase
Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)

Physical

MOL	4.57
MOD	2.38
Weight (lb.)	0.14

Additional Information

Rated For Enclosed Fixture	Yes
Warranty	3 Year Limited

Compliance

Safety Listing	cULus Listed
Location Rating	Damp
Energy Star	No
California Status	Non-Compliant
RoHS Compliant	Yes
SDS Sheet	LED_Lamp