

Project Name

Location

Prepared By



# SATCO S39718

25T5/LED/46-840/BP/HO/SE-DE

**Notes**

[www] 06-09-2021 01:41:23

**General**

Status	Active
Watts	25W
Fluorescent Equivalent	54W
Volts	120V-277V
Ballast Type	Type B
Shape	T5
Base	Miniature Bi Pin
ANSI Base	G5
Nominal Length	48
Finish	Frost
CCT (Kelvin)	4000
Temperature	Cool White
CRI	83
Lumens	3300L
Beam Spread	240
Dimmable	Non-Dimmable
Hours Rated	50000
Lamp Type	Linear
Technology	LED

**Electrical**

Operating Frequency	50/60 Hz
Power Factor	0.9
THD	20%
Operating Temperature	-25C (-13F) to a maximum of +45C (+113F)

**Physical**

MOL	46
MOD	0.83
Material	Glass
Lens Finish	Frost
Lens Material	Glass
Housing Color	White
Weight (lb.)	0.4

**Additional Information**

Shatter-Proof Type	PET Coated
Warranty	5 Year Limited - T5 LED Bulbs - Ballast Bypass

**Compliance**

Safety Listing	cULus Classified
Location Rating	Damp
Energy Star	No
DLC Approved	Yes
DLC ID	PLNRT1RABCIP
California Status	Lawful for sale
RoHS Compliant	Yes
FCC Compliant	Yes
NSF Approved	Yes

