

Project Name

Location

Prepared By



# SATCO S39719

25T5/LED/46-850/BP/HO/SE-DE

**Notes**

[www] 06-09-2021 01:41:23

**General**

|                        |                  |
|------------------------|------------------|
| Status                 | Active           |
| Watts                  | 25W              |
| Fluorescent Equivalent | 54W              |
| Volts                  | 120V-277V        |
| Ballast Type           | Type B           |
| Shape                  | T5               |
| Base                   | Miniature Bi Pin |
| ANSI Base              | G5               |
| Nominal Length         | 48               |
| Finish                 | Frost            |
| CCT (Kelvin)           | 5000             |
| Temperature            | Natural Light    |
| CRI                    | 83               |
| Lumens                 | 3400L            |
| Beam Spread            | 240              |
| Dimmable               | Non-Dimmable     |
| Hours Rated            | 50000            |
| Lamp Type              | Linear           |
| Technology             | LED              |

**Electrical**

|                       |  |
|-----------------------|--|
| Operating Frequency   | 50/60 Hz                                 |
| Power Factor          | 0.9                                      |
| THD                   | 20%                                      |
| Operating Temperature | -25C (-13F) to a maximum of +45C (+113F) |

**Physical**

|               |       |
|---------------|-------|
| MOL           | 46    |
| MOD           | 0.83  |
| Material      | Glass |
| Lens Finish   | Frost |
| Lens Material | Glass |
| Housing Color | White |
| Weight (lb.)  | 0.4   |

**Additional Information**

|                    |  |
|--------------------|--|
| Shatter-Proof Type | PET Coated                                     |
| Warranty           | 5 Year Limited - T5 LED Bulbs - Ballast Bypass |

**Compliance**

|                   |                  |
|-------------------|------------------|
| Safety Listing    | cULus Classified |
| Location Rating   | Damp             |
| Energy Star       | No               |
| DLC Approved      | Yes              |
| DLC ID            | PLYF62HN8A9I     |
| California Status | Lawful for sale  |
| RoHS Compliant    | Yes              |
| FCC Compliant     | Yes              |
| NSF Approved      | Yes              |

