

Project Name

Location

Prepared By



SATCO S39769

75W/LED/HID/MB-G3/50K/100-277V

Notes

[www] 11-22-2021 02:57:43

General

Status	Active
Watts	75W
Incandescent Equivalent	750W
Fluorescent Equivalent	105W
HID Equivalent	400W
Volts	100V-277V
Shape	Corncob
Base	Mogul Extended
ANSI Base	EX39
Finish	Clear
CCT (Kelvin)	5000
Temperature	Natural Light
CRI	80
Lumens	10500L
Beam Spread	120;150;260
Dimmable	Non-Dimmable
Hours Rated	50000
Lamp Type	LED HID
Technology	LED
Min Compartment Size	Width: 9.30 in. Depth: 9.30 in. Height: 10.50 in.

Electrical

Operating Frequency	50/60 Hz
Power Factor	>0.9
Surge Protection	Built-in surge protection - 4KV
THD	<20%
Operating Temperature	-20C (-4F) to a maximum of +65C (+149F)

Physical

MOL	8.46
MOD	4.13
Lens Finish	Clear
Lens Material	Thermo Plastic (PBT)
Housing Color	White
Photocell	Optional Add-On
Weight (lb.)	2.40

Additional Information

Additional Info	PIR Sensor available as an accessory
Rated For Enclosed Fixture	Yes
IP Rating	IP64
Specification Note	Closed 260 deg; Partial 150 deg; Open 120 deg
Warranty	5 Year Limited - Hi-Pro

Compliance

Safety Listing	cULus Classified
Location Rating	Damp
Energy Star	No
DLC Approved	Yes

DLC ID	PLHA08Z553YE
California Status	Lawful for sale
RoHS Compliant	Yes
FCC Compliant	Yes
SDS Sheet	LED_Lamp

Copyright 2020 Satco Products, Inc.
All Rights Reserved

For More Information Visit:
<http://www.satco.com/>

