

Project Name

Location

Prepared By



SATCO S11431

5A19/LED/850/AGRI/120V/D

Notes

[www] 11-22-2021 02:57:41

General

| | |
|-------------------------|---------------|
| Status | Active |
| Watts | 5W |
| Incandescent Equivalent | 40W |
| Volts | 120V |
| Shape | A19 |
| Base | Medium |
| ANSI Base | E26 |
| Finish | Frost |
| CCT (Kelvin) | 5000 |
| Temperature | Natural Light |
| CRI | 80 |
| Lumens | 550L |
| Beam Spread | 140 |
| Dimmable | Yes-Dimmable |
| Hours Rated | 25000 |
| Lamp Type | Type A |
| Technology | LED |

Electrical

| | |
|-----------------------|--|
| Operating Frequency | 60 Hz |
| Dimming Type | Forward Phase or Reverse Phase or Phase Selectable |
| Power Factor | 0.9 |
| Operating Temperature | -20C (-4F) to a maximum of +45C (+113F) |

Physical

| | |
|---------------|-------|
| MOL | 4.61 |
| MOD | 2.36 |
| Housing Color | White |
| Weight (lb.) | 0.11 |

Additional Information

| | |
|----------------------------|--------------------------------|
| Rated For Enclosed Fixture | Yes |
| Warranty | 3 Year Limited - 16 hr per day |

Compliance

| | |
|-------------------|---------------|
| Safety Listing | cULus Listed |
| Location Rating | Wet |
| Energy Star | No |
| California Status | Non-Compliant |
| RoHS Compliant | Yes |
| SDS Sheet | LED_Lamp |