

Project Name

Location

Prepared By



SATCO S11433

8.5A19/LED/850/AGRI/120V/D

Notes

[www] 11-22-2021 02:57:41

General

Status	Active
Watts	8.5W
Incandescent Equivalent	60W-75W
Volts	120V
Shape	A19
Base	Medium
ANSI Base	E26
Finish	Frost
CCT (Kelvin)	5000
Temperature	Natural Light
CRI	80
Lumens	1000L
Beam Spread	140
Dimmable	Yes-Dimmable
Hours Rated	25000
Lamp Type	Type A
Technology	LED

Electrical

Operating Frequency	60 Hz
Dimming Type	Forward Phase or Reverse Phase or Phase Selectable
Power Factor	0.9
Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)

Physical

MOL	4.61
MOD	2.36
Housing Color	White
Weight (lb.)	0.11

Additional Information

Rated For Enclosed Fixture	Yes
Warranty	3 Year Limited - 16 hr per day

Compliance

Safety Listing	cULus Listed
Location Rating	Wet
Energy Star	No
California Status	Non-Compliant
RoHS Compliant	Yes
SDS Sheet	LED_Lamp