

Project Name

Location

Prepared By



SATCO S11251

4.5G25/LED/TW/CL/SF

Notes

[www] 06-27-2021 00:19:10

General

Status	Active
Watts	4.5W
Incandescent Equivalent	40W
Volts	120V
Shape	G25
Base	Medium
ANSI Base	E26
Finish	Clear
CCT (Kelvin)	2700K-5000K
Temperature	Warm to Cool White
CRI	80
Lumens	450L
Beam Spread	280
Dimmable	Yes-Dimmable
Hours Rated	15000
Lamp Type	Globe
Technology	LED

Smart Product Info

IOT Enabled	Yes
Operational Humidity	10% - 80% R.H.
Number of Switching Cycles	7500
Software Upgradeable	Yes
Start Up	0.5S
Communication Protocol	WiFi-2.4GHz
Voice Assistants Supported	Siri Shortcuts; Alexa; Hey Google; SmartThings
Software Supported	Tuya/Starfish APP

Electrical

Operating Frequency	60 Hz
---------------------	-------

Specifications

Power Factor	0.5
Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)

Physical

MOL	4.45
MOD	3.15
Lens Finish	Clear
Weight (lb.)	0.11

Additional Information

Rated For Enclosed Fixture	Yes
Warranty	3 Year Limited - 3 hr per day

Compliance

Safety Listing	cULus
Location Rating	Damp
Energy Star	No
California Status	Non-Compliant
RoHS Compliant	Yes

FCC Compliant	Yes
SDS Sheet	LED_Lamp

Copyright 2020 Satco Products, Inc.
All Rights Reserved

For More Information Visit:
<http://www.satco.com/>

