

Project Name

Location

Prepared By



# SATCO S11254

10A19/LED/RGB/TW/T20/SF

**Notes**

[www] 11-22-2021 02:57:41

**General**

Status	Active
Watts	10W
Incandescent Equivalent	60W
Volts	120V
Shape	A19
Base	Medium
ANSI Base	E26
Finish	White
CCT (Kelvin)	2700K-5000K
Temperature	Warm to Cool White/Color Changeable
CRI	90
Lumens	800L
Beam Spread	220
Dimmable	Yes-Dimmable
Hours Rated	15000
Lamp Type	Type A
Technology	LED

**Smart Product Info**

IOT Enabled	Yes
Operational Humidity	-10C - +45C
Number of Switching Cycles	7500
Software Upgradeable	Yes
Start Up	100% coldlight
Communication Protocol	WiFi
Voice Assistants Supported	Siri; Alexa; Hey Google; SmartThings
Software Supported	Tuya/Starfish APP

**Electrical**

Operating Frequency	60 Hz
---------------------	-------

**Specifications**

Power Factor	0.7
Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)

**Physical**

MOL	4.57
MOD	2.36
Lens Finish	Plastic (PS)
Lens Material	Plastic (PS)
Weight (lb.)	0.16

**Additional Information**

Rated For Enclosed Fixture	Yes
Warranty	3 Year Limited - 3 hr per day

**Compliance**

Safety Listing	cULus
Location Rating	Damp
Energy Star	Yes
ES Unique ID	ESID-2368816

California Status	Lawful for sale
RoHS Compliant	Yes
FCC Compliant	Yes
SDS Sheet	LED_Lamp

Copyright 2020 Satco Products, Inc.  
All Rights Reserved

For More Information Visit:  
<http://www.satco.com/>

