

Project Name

Location

Prepared By



SATCO S11257

9.5BR30/LED/RGB/TW/T20/SF

Notes

[www] 06-27-2021 00:19:10

General

Status	Active
Watts	9.5W
Incandescent Equivalent	65W
Volts	120V
Shape	BR30
Base	Medium
ANSI Base	E26
Finish	White
CCT (Kelvin)	2700K-5000K
Temperature	Warm to Cool White/Color Changeable
CRI	90
Lumens	760L
Beam Spread	100
Dimmable	Yes-Dimmable
Hours Rated	25000
Lamp Type	Reflector
Technology	LED

Smart Product Info

IOT Enabled	Yes
Operational Humidity	-10C - +45C
Number of Switching Cycles	12500
Software Upgradeable	Yes
Start Up	100% coldlight
Communication Protocol	WiFi
Voice Assistants Supported	Siri; Alexa; Hey Google; SmartThings
Software Supported	Tuya/Starfish APP

Electrical

Operating Frequency	60 Hz
---------------------	-------

Specifications

Power Factor	0.7
Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)

Physical

MOL	5.12
MOD	3.70
Lens Finish	White
Weight (lb.)	0.21

Additional Information

Rated For Enclosed Fixture	Yes
Warranty	3 Year Limited - 3 hr per day

Compliance

Safety Listing	cULus
Location Rating	Damp
Energy Star	Yes
ES Unique ID	ESID-2368864
California Status	Lawful for sale

RoHS Compliant	Yes
FCC Compliant	Yes
SDS Sheet	LED_Lamp

Copyright 2020 Satco Products, Inc.
All Rights Reserved

For More Information Visit:
<http://www.satco.com/>

