

Project Name

Location

Prepared By



SATCO S11259

8.7W/LED/RDL/4/TW/T20/JA8/SF

Notes

[www] 06-27-2021 00:19:10

General

Status	Active
Finish	White
Wattage	8.7W
CCT (Kelvin)	2700K-5000K
Color Temperature	Warm to Cool White
Width (in.)	5.12
Height (in.)	2.80
Indoor or Outdoor Fixture	Indoor

Smart Product Info

IOT Enabled	Yes
Operational Humidity	-10C - +45C
Life Cycles	12500
Software Upgradeable	Yes
Start Up	100% coldlight
Communication Protocol	WiFi
Voice Assistants Supported	Siri Shortcuts; Alexa; Hey Google; SmartThings
Software Supported	Tuya/Starfish APP

Specifications

Technology	LED
CRI	90
Lumen Output	700L
Rated Hours	25000
Voltage	120V
Dimmable	Yes-Dimmable
Beam Angle	90
Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)
IC Rated	Yes
Weight (lb.)	0.34
Fixture Shape	Round
Fixture Material	Metal
Fixture Type	Downlight Retrofit

Compliance

Safety Listing	cULus Classified; cULus Listed
Location Rating	Wet
Energy Star	Yes
ES Unique ID	ESID-2371661
California Status	California T24 Compliant
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	Yes

Additional Information

Includes	E26 Adapter
Warranty	5 Year Limited - 3 hr per day

