

Project Name

Location

Prepared By



SATCO S11262

12WLED/DW/6"/TW/RD/SF

Notes

[www] 11-29-2021 04:01:41

General

Status	Active
Finish	White
Wattage	12W
CCT (Kelvin)	2700K-5000K
Color Temperature	Warm to Cool White
Width (in.)	7.20
Height (in.)	1.50
Indoor or Outdoor Fixture	Indoor

Smart Product Info

IOT Enabled	Yes
Operational Humidity	-20C - +40C
Life Cycles	25000
Software Upgradeable	Yes
Start Up	100% coldlight
Communication Protocol	WiFi
Voice Assistants Supported	Siri Shortcuts; Alexa; Hey Google; SmartThings
Software Supported	Tuya/Starfish APP

Specifications

Technology	LED
CRI	80
Lumen Output	850L
Rated Hours	25000
Voltage	120V
Dimmable	Yes-Dimmable
Beam Angle	110
Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)
IC Rated	Yes
Weight (lb.)	1.03
Fixture Shape	Round
Fixture Material	Steel
Fixture Type	Remote Driver LED Downlight

Compliance

Safety Listing	cETLus
Location Rating	Wet
Energy Star	Yes
ES Unique ID	ESID-2371664
California Compliant Substitute	S11280
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	Yes

Additional Information

Warranty	5 Year Limited - 3 hr per day
----------	-------------------------------