

Project Name

Location

Prepared By



## SATCO S11263

20W/LED/STRIP/IP20/SF/6FT

### Notes

[www] 11-08-2021 02:55:03

### General

Status	Active
Finish	White
Wattage	20W
CCT (Kelvin)	3000K-6500K
Color Temperature	Warm to Cool White
Length (in.)	72.00
Width (in.)	0.47
Height (in.)	0.12
Indoor or Outdoor Fixture	Indoor

### Smart Product Info

IOT Enabled	Yes
Operational Humidity	0-85%
Life Cycles	15000
Software Upgradeable	Yes
Start Up	1s
Communication Protocol	Wifi
Voice Assistants Supported	Siri Shortcuts; Alexa; Hey Google; SmartThings
Software Supported	Tuya/Starfish APP

### Specifications

Technology	LED
CRI	80
Lumen Output	1600L
Rated Hours	25000
Voltage	120V
Dimmable	Yes-Dimmable
Beam Angle	120
Operating Temperature	-20C (-4F) to a maximum of +40C (+104F)
Weight (lb.)	0.46
Up/Down Installation	Up/Down and Vertical
Fixture Material	Plastic
Fixture Type	Tape Light

### Compliance

Safety Listing	cETLus
Location Rating	Damp
Energy Star	No
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	Yes

### Additional Information

Installation Notes	Includes power supply: input: AC100 240-Volt 0.6A 50-60 Hz, output: 12-Volt, 20-Watt
Warranty	1 Year Limited - Smart Products

