

Project Name

Location

Prepared By



SATCO S11264

8W/LED/STRIP/IP20/SF/3FT-EXT

Notes

[www] 11-06-2021 02:55:03

General

Status	Active
Finish	White
Wattage	8W
CCT (Kelvin)	3000K-6500K
Color Temperature	Warm to Cool White
Length (in.)	39.37
Width (in.)	0.47
Height (in.)	0.12
Indoor or Outdoor Fixture	Indoor

Smart Product Info

IOT Enabled	Yes
Operational Humidity	0-85%
Software Upgradeable	Yes
Voice Assistants Supported	Siri Shortcuts; Alexa; Hey Google; SmartThings

Specifications

Technology	LED
CRI	80
Lumen Output	800L
Rated Hours	25000
Voltage	120V
Dimmable	Yes-Dimmable
Beam Angle	120
Operating Temperature	-20C (-4F) to a maximum of +40C (+104F)
Weight (lb.)	0.09
Up/Down Installation	Up/Down and Vertical
Fixture Material	Plastic
Fixture Type	Tape Light
Max. Connectable Units	8

Compliance

Safety Listing	cETLus
Location Rating	Damp
Energy Star	No
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	Yes

Additional Information

Installation Notes	This product consumes a total of 20W (.167A) and is rated to control up to 8 additional S11264 extension strips. Each extension strip consumes 8.8W (.075A.)
Warranty	1 Year Limited - Smart Products