

Project Name

Location

Prepared By



Notes

[www] 11-06-2021 02:55:03

General

Status	Active
Finish	White
Wattage	28W
CCT (Kelvin)	2700K-6500K
Color Temperature	Warm to Cool White
Length (in.)	192
Width (in.)	0.47
Height (in.)	0.12
Indoor or Outdoor Fixture	Indoor and Outdoor

Smart Product Info

IOT Enabled	Yes
Operational Humidity	0-85%
Life Cycles	15000
Software Upgradeable	Yes
Start Up	1s
Communication Protocol	Wifi
Voice Assistants Supported	Siri Shortcuts; Alexa; Hey Google; SmartThings
Software Supported	Tuya/Starfish APP

Specifications

Technology	LED
CRI	80
Lumen Output	2500L
Rated Hours	25000
Voltage	120V
Dimmable	Yes-Dimmable
Beam Angle	120
Operating Temperature	-20C (-4F) to a maximum of +40C (+104F)
Weight (lb.)	1.10
Up/Down Installation	Up/Down and Vertical
Fixture Material	Plastic
Fixture Type	Tape Light

Compliance

Safety Listing	cETLus
Location Rating	Wet
Energy Star	No
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	Yes

Additional Information

Additional Information	Silicone Sleeve - IP65 - Do Not Cut
Installation Notes	Includes power supply: input: AC100 120-Volt 0.6A 50-60 Hz, output: 12-Volt, 28-Watt
Warranty	1 Year Limited - Smart Products



