

Project Name

Location

Prepared By



Notes

[www] 03-01-2021 00:54:13

General

Status	Active
Finish	Black
Wattage	10
CCT (Kelvin)	2700
Color Temperature	Warm White & RGBW Color Changing
Length (in.)	288
Width (in.)	1.77
Height (in.)	7.48
Indoor or Outdoor Fixture	Indoor and Outdoor

Smart Product Info

IOT Enabled	Yes
Voice Assistants Supported	Siri Shortcuts; Alexa; Hey Google; SmartThings

Specifications

Technology	LED
CRI	80
Lumen Output	260
Rated Hours	15000
Voltage	120V
Dimmable	Dimmable Only with Starfish App
Recommended Dimmer	Smart
Beam Angle	120
Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)
Weight (lb.)	3.51
Fixture Material	Plastic
Fixture Type	String Light

Dimensions

Wire Length	24 ft.
-------------	--------

Compliance

Safety Listing	cETLus
Location Rating	Wet
Energy Star	No
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	Yes

Additional Information

Warranty	3 Year Limited - 3 hr per day
----------	-------------------------------