

## **SATCO S49978**

14/T8/LED/48-850/DR

Notes

General	
Status	Active
Watts	14
Fluorescent Equivalent	32W/30W/28W/25W
Volts	120V-270V
Ballast Type	Type A
Shape	Т8
Base	Medium Bi Pin
ANSI Base	G13
Nominal Length	48
Finish	Gloss White
CCT (Kelvin)	5000
Temperature	Natural Light
CRI	82
Lumens	2200
Beam Spread	210
Dimmable	Check Ballast MFG for Dimmer Compatibility
Hours Rated	50000
Lamp Type	Linear
Technology	LED
Electrical	
Operating Frequency	50/60 Hz
Power Factor	0.9
THD	20%
Operating Temperature	-20C (-4F) to a maximum of +45C

Electrical	
Operating Frequency	50/60 Hz
Power Factor	0.9
THD	20%
Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)

Physical	
MOL	48
MOD	1.1
Material	Glass
Lens Finish	Frosted
Lens Material	Glass
Housing Color	White

Lens i illish	1 103160
Lens Material	Glass
Housing Color	White
Additional Information	
Warranty	5 Year Limited - T8 LED Bulbs

Compliance	
Safety Listing	cULus
Location Rating	Damp
Energy Star	No
DLC Approved	Yes
DLC ID	PLOM3FSPOZYT
California Status	Lawful for sale in California
Nevada Status	Lawful for sale in Nevada
RoHS Compliant	Yes
FCC Compliant	Yes
NSF Approved	Yes

For More Information Visit: https://www.satco.com/

















