

Project Name

Location

Prepared By



SATCO S22214

8.5PAR30L/LED/930/FL/120V

Notes

[www] 06-14-2021 17:39:05

General

| | |
|-------------------------|--------------|
| Status | Active |
| Watts | 8.5 |
| Incandescent Equivalent | 75 |
| Volts | 120V |
| Shape | PAR 30L |
| Base | Medium |
| ANSI Base | E26 |
| Finish | Clear |
| CCT (Kelvin) | 3000 |
| Temperature | Soft White |
| CRI | 90 |
| Lumens | 700 |
| Beam Spread | 40 |
| Dimmable | Yes-Dimmable |
| Hours Rated | 15000 |
| Lamp Type | PAR |
| Technology | LED |

Electrical

| | |
|---------------------|-------|
| Operating Frequency | 60 Hz |
| Candlepower | 75 |
| Dimming Type | Triac |
| Power Factor | 0.7 |

Physical

| | |
|---------------|-------------|
| MOL | 4.41 |
| MOD | 3.74 |
| Lensed | Lensed Lamp |
| Lens Material | Plastic |
| Housing Color | White |
| Weight (lb.) | 0.04 |

Additional Information

| | |
|----------------------------|----------------|
| Rated For Enclosed Fixture | Yes |
| Warranty | 3 Year Limited |

Compliance

| | |
|-------------------|-------------------------------|
| Safety Listing | cULus Listed |
| Location Rating | Wet |
| Energy Star | No |
| California Status | Lawful for sale in California |
| RoHS Compliant | Yes |
| FCC Compliant | Yes |
| SDS Sheet | LED_Lamp |