

Project Name

Location

Prepared By



## SATCO S22215

8.5PAR30L/LED/940/FL/120V

Notes

[www] 06-14-2021 17:39:05

### General

Status	Active
Watts	8.5
Incandescent Equivalent	75
Volts	120V
Shape	PAR 30L
Base	Medium
ANSI Base	E26
Finish	Clear
CCT (Kelvin)	4000
Temperature	Cool White
CRI	90
Lumens	700
Beam Spread	40
Dimmable	Yes-Dimmable
Hours Rated	15000
Lamp Type	PAR
Technology	LED

### Electrical

Operating Frequency	60 Hz
Candlepower	75
Dimming Type	Triac
Power Factor	0.7

### Physical

MOL	4.41
MOD	3.74
Lensed	Lensed Lamp
Lens Material	Plastic
Housing Color	White
Weight (lb.)	0.04

### Additional Information

Rated For Enclosed Fixture	Yes
Warranty	3 Year Limited

### Compliance

Safety Listing	cULus Listed
Location Rating	Wet
Energy Star	No
California Status	Lawful for sale in California
RoHS Compliant	Yes
FCC Compliant	Yes
SDS Sheet	LED_Lamp