

Project Name

Location

Prepared By



SATCO S29918

40T8/LED/96-840/BP/FA8

Notes

[www] 06-30-2021 01:33:09

General

Status	Active
Watts	40W
Fluorescent Equivalent	59W
Volts	120V-277V
Ballast Type	Type B
Shape	T8
Base	Single Pin
ANSI Base	FA8
Nominal Length	96.00
Finish	White
CCT (Kelvin)	4000
Temperature	Cool White
CRI	82
Lumens	5500L
Beam Spread	210
Dimmable	Non-Dimmable
Hours Rated	50000
Lamp Type	Linear
Technology	LED

Electrical

Ballasting Requirements	Ballast Bypass
Power Factor	0.9
THD	25%
Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)

Physical

MOL	94.00
MOD	1.00
Material	Glass
Lens Finish	White
Weight (lb.)	0.88

Additional Information

Additional Info	Suitable for Emergency Lighting only with Satco EM Driver #S8002
Shatter-Proof Type	PET Coated
Warranty	5 Year Limited - T8 LED Bulbs

Compliance

Safety Listing	cULus
Location Rating	Damp
Energy Star	No
DLC Approved	Yes
DLC ID	PL10N0GDSU9Z
California Status	Lawful for sale in California
RoHS Compliant	Yes
FCC Compliant	Yes
NSF Approved	Yes



